

# **MS 128 E**

## Static holding trolley



### **CONSTRUCTION FEATURES**

- Tightness chamber with radiuses corners
- Plastic bumpers
- Total thermic insulation with rock or glass wood
- Long lasting front and door seals made up of food glade of high heat resistance
- Double door to reduce mostly the drop in temperature at opening
- Removable si de racks to facilitate cleaning
- Static heating provided by low consumption wise heating element that colis up all the chamber
- Snap-shut doors
- Mounted on four 150 mm diameter castors, two of witch with brake
- Ergonomic handles for pushing and guiding
- Easy access to facilitate maintenance and repair

### **FUNCTIONAL FEATURES**

- Electronic control of the temperature
- Operating temperature 30°÷120°C
- Two adjustable humidity vents on the door
- Chamber with safety thermostat


#### **STANDARD SUPPLY**

• Two shelves with grid GN2/1 each door

### **OPTIONS & ACCESSORIES**

- Stainless steel plate baskets
- Additional shelves with grid GN2/1
- Guides for gastronorm containers






Ε

START/STOP key

### **TECHNICAL INSTALLATION DIAGRAM**



45 5024	Model	Overall dimensions (W x D x H) - mm	Trays capacity	Plates capacity ø260	Plates capacity ø320	Power kW	Power supply	
MS 128 E 1175 x 855 x 1820 h 16 X GN 2/1 128 96 2,25 AC 230 V / 50 I	MS 128 E	1175 x 855 x 1820 h	16 x GN 2/1 32 x GN 1/1	128	96	2,25	AC 230 V / 50 Hz	



Electricity supply cable inlet

Adjustable vent for release of excess humidity